





Dimensions in mm (inches).





## TO39 (TO205AD) PINOUTS

3 - Collector

1 – Emitter 2 – Base

Bipolar NPN Device in a Hermetically sealed TO39 Metal Package.

## **Bipolar NPN Device.**

$$V_{CEO} = 300V$$

$$I_{c} = 0.1A$$

All Semelab hermetically sealed products can be processed in accordance with the requirements of BS, CECC and JAN, JANTX, JANTXV and JANS specifications

Parameter	Test Conditions	Min.	Тур.	Max.	Units
V <sub>CEO</sub> *				300	V
I <sub>C(CONT)</sub>				0.1	Α
h <sub>FE</sub>	@ 10/20m ( $V_{\rm CE}$ / $I_{\rm C}$ )	100		300	-
f <sub>t</sub>			200M		Hz
P <sub>D</sub>				1	W
* Maximum Working Voltage					

This is a shortform datasheet. For a full datasheet please contact <a href="mailto:sales@semelab.co.uk">sales@semelab.co.uk</a>.

Semelab PIc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use.

## This datasheet has been downloaded from:

www. Data sheet Catalog.com

Datasheets for electronic components.