

For Single Photon Counting, Dark Counts 50 s<sup>-1</sup> Typ. at 25 °C  
For Extremely Low Light Level Detection

28 mm (1-1/8 Inch) Diameter, 9-stage, Multialkali Photocathode, Side-On Type  
185 nm to 850 nm Spectral Response

## SPECIFICATIONS

### GENERAL

Parameter		Description/Value	Unit
Spectral Response		185 to 850	nm
Wavelength of Maximum Response		430	nm
Photocathode	Material	Multialkali	—
	Minimum Effective Area	8 × 24	mm
Window Material		UV glass	—
Dynode	Structure	Circular-cage	—
	Number of Stages	9	—
Direct Interelectrode Capacitances	Anode to Last Dynode	Approx. 4	pF
	Anode to All Other Electrodes	Approx. 6	pF
Base		11-pin base JEDEC No. B11-88	—
Weight		Approx. 45	g
Operating Ambient Temperature		-30 to +50	°C
Storage Temperature		-30 to +50	°C
Suitable Socket		E678-11A (Sold Separately)	—
Suitable Socket Assembly		E717-63 (Sold Separately)	—



### MAXIMUM RATINGS (Absolute Maximum Values)

Parameter		Value	Unit
Supply Voltage	Between Anode and Cathode	1250	V
Average Anode Current	Between Anode and Last Dynode	250	V
		0.1	mA

### CHARACTERISTICS (at 25 °C)

Parameter		Min.	Typ.	Max.	Unit	
Cathode Sensitivity	Luminous (2856K)	140	200	—	μA/lm	
	Quantum Efficiency	at 400 nm	—	23.7	—	%
		at 500 nm	—	18.3	—	%
		at 600 nm	—	10.7	—	%
		at 700 nm	—	2.7	—	%
	at 800 nm	—	0.56	—	%	
	Red/White Ratio	0.1	0.15	—	—	
	Blue Sensitivity Index (CS 5-58)	—	7.5	—	—	
Anode Sensitivity	Luminous (2856K)	300	700	—	A/lm	
Gain		—	3.5 × 10 <sup>6</sup>	—	—	
Dark Counts *		—	50	100	s <sup>-1</sup>	
Anode Dark Current (After 30 min Storage in Darkness)		—	0.2	1	nA	
Time Response	Anode Pulse Rise Time	—	2.2	—	ns	
	Electron Transit Time	—	22	—	ns	
	Transit Time Spread (TTS)	—	1.2	—	ns	


\* Measured at the voltage producing the gain of 1 × 10<sup>6</sup>

### VOLTAGE DISTRIBUTION RATIO AND SUPPLY VOLTAGE

Electrodes	K	Dy1	Dy2	Dy3	Dy4	Dy5	Dy6	Dy7	Dy8	Dy9	P
Ratio	1	1	1	1	1	1	1	1	1	1	1

Supply Voltage: 1000 V, K: Cathode, Dy: Dynode, P: Anode

Figure 1: Typical Spectral Response



# PHOTOMULTIPLIER TUBES R4632

Figure 2: Anode Luminous Sensitivity and Gain Characteristics




Figure 3: Dimensional Outline and Basing Diagram (Unit: mm)





Figure 4: Accessories (Unit: mm) Sold Separately

### D Type Socket Assembly E717-63



\* Hamamatsu also provides C4900 series compact high voltage power supplies and C6270 series DP type socket assemblies which incorporate a DC to DC converter type high voltage power supply.

**Warning—Personal Safety Hazards**  
Electrical Shock—Operating voltages applied to this device present a shock hazard.

# HAMAMATSU

WEB SITE [www.hamamatsu.com](http://www.hamamatsu.com)

HAMAMATSU PHOTONICS K.K., Electron Tube Division

314-5, Shimokanzo, Iwata City, Shizuoka Pref., 438-0193, Japan, Telephone: (81)539/62-5248, Fax: (81)539/62-2205

U.S.A.: Hamamatsu Corporation: 360 Foothill Road, P. O. Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1)908-231-0960, Fax: (1)908-231-1218 E-mail: [usa@hamamatsu.com](mailto:usa@hamamatsu.com)

Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-2658 E-mail: [info@hamamatsu.de](mailto:info@hamamatsu.de)

France: Hamamatsu Photonics France S.A.R.L.: 19, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 00, Fax: (33)1 69 53 71 10 E-mail: [infos@hamamatsu.fr](mailto:infos@hamamatsu.fr)

United Kingdom: Hamamatsu Photonics UK Limited: 2 Howard Court, 10 Tewin Road Welwyn Garden City Hertfordshire AL7 1BW, United Kingdom, Telephone: 44-(0)1707-294888, Fax: 44(0)1707-325777 E-mail: [info@hamamatsu.co.uk](mailto:info@hamamatsu.co.uk)

North Europe: Hamamatsu Photonics Norden AB: Smidesvägen 12, SE-171-41 SOLNA, Sweden, Telephone: (46)8-509-031-00, Fax: (46)8-509-031-01 E-mail: [info@hamamatsu.se](mailto:info@hamamatsu.se)

Italy: Hamamatsu Photonics Italia: S.R.L.: Strada della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39)02-935 81 733, Fax: (39)02-935 81 741 E-mail: [info@hamamatsu.it](mailto:info@hamamatsu.it)

TPMS1046E02  
JUL. 2006. IP