

DESCRIPTION:

The KWM-37881XY series is 38.00mm (1.496") height 8 x 8 multi-color dot matrix display.

This multi-color series is suitable for use in single/multi-line message display, large area graphics display and electronic games.

All devices are available as either common row anode or common row cathode.

ABSOLUTE MAXIMUM RATINGS: (Ta=25°C)


Parameter	Max
Reverse Voltage per segment	5 V
Reverse Current per segment (Vr = 5V)	100μA
Derating Linear from 25°C per segment	0.4mA/°C
Operating Temperature Range	-40°C To 85°C
Storage Temperature Range	-40°C To 100°C
Soldering Temperature 1.6mm(1/16") from body for 5 sec. at 260°C	

- NOTES : 1. All dimensions are in millimeters (inches).
 2. Tolerance is ±0.25mm(0.010) unless otherwise specified.
 3. Specifications are subject to change without notice.
 4. NP: No Pin.
 5. NC: No Connect.


TESTING CONDITION FOR EACH PARAMETER :

Parameter	Symbol	Unit	Test Condition
Forward Voltage	Vf	V	If=20mA
Peak Emission Wave Length	λp	nm	If=20mA
Spectral Line Half-Width	Δλ	nm	If=20mA
Reverse Current	Ir	μA	Vr=5V
Average Luminous Intensity	Iv	μ cd	If=10mA

PACKAGE DIMENSIONS



INTERNAL CIRCUIT DIAGRAM



PART NO. SELECTION AND APPLICATION INFORMATION (RATINGS AT 25°C AMBIENT)

Part No.	Chip		C.C or C.A	Wave Length λp (nm)	Absolute Maximum Ratings				Electro-optical Characteristic						
	Raw Material	Emitted Color			Δλ (nm)	Pd (mW)	If (mA)	If (Peak) (mA)	Vf (V) Per Dot			If (Rec) (mA)	Iv (μcd) Per Dot		
									Min.	Typ.	Max.		Min.	Typ.	
KWM-37881A32	GaAsP/GaP	Hi-Eff Red	Common Anode	635	45	100	50	100	1.7	1.9	2.6	10-20	850	1500	
	GaP	Green		565	30	100	50	100	1.7	2.2	2.6	10-20	750	1400	
KWM-37881ASG	GaAlAs	Super Red		660	20	100	50	100	1.5	1.9	2.6	10-20	1500	3000	
	GaP	Super Green		570	30	100	50	100	1.7	2.2	2.6	10-20	800	1550	
KWM-37881A62	GaAsP/GaP	Yellow		585	30	100	50	100	1.7	1.9	2.6	10-20	750	1400	
	GaP	Green		565	30	100	50	100	1.7	2.2	2.6	10-20	750	1400	
KWM-37881C32	GaAsP/GaP	Hi-Eff Red		Common Cathode	635	45	100	50	100	1.7	1.9	2.6	10-20	850	1500
	GaP	Green			565	30	100	50	100	1.7	2.2	2.6	10-20	750	1400
KWM-37881CSG	GaAlAs	Super Red			660	20	100	50	100	1.5	1.9	2.6	10-20	1500	3000
	GaP	Super Green			570	30	100	50	100	1.7	2.2	2.6	10-20	800	1550
KWM-37881C62	GaAsP/GaP	Yellow	585		30	100	50	100	1.7	1.9	2.6	10-20	750	1400	
	GaP	Green	565		30	100	50	100	1.7	2.2	2.6	10-20	750	1400	

- REMARKS : 1. The average luminous intensity is obtained by summing the luminous intensity of each segment and dividing by the total number of segments.
 2. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (International Commission on Illumination) eye-response curve.
 3. Clean only by pure water, isopropanol, ethanol, Freon TF (or equivalent).