High Power PIN Photodiode Receiver



MICROWAVE



Features

- Highly reliable planar photodiode technology
- High power capability
- Bandwidth up to 5 GHz
- Good RF matching, 12 dB typ.

Applications

- Antenna Remoting
- Military Communications
- **Phased Arrays**
- **EW**
- Delay Lines for Radar Calibration


The 10458C PIN microwave photodiode receiver incorporates a high-speed planar PIN photodiode, with low-noise bias and monitor electronics. The units installs in Emcore's System 10000 3RU equipment rack providing a highly reliable, highpower photodiode receiver. The receiver is well matched over the operating frequency band, thereby simplifying high-speed integration.



Performance Highlights

Parameter	Min	Typical	Max	Units
Storage Temperature	-40	-	+85	°C
Operating Temperature	-10	25	+50	°C
Responsivity	0.7	-	-	A/W
Receiver Gain (1 GHz)	-9.1	-	-	dB (A/W)
Dark Current (25C)	-	-	5	nA
Max Current	-	-	10	mA
Optical Input	-	-	11	dBm
RF Return Loss	8	12	-	dB
Optical Wavelength Range	1280	-	1580	nm
Optical Return Loss	-	-	-40	dB
Module DC Current (Pin 1)	-	-	200	mA

Typical S21 Data



50 MHz 22 GHz

RF Characteristics

Parameter	Symbol	Condition	Min	Typical	Max	Units
Bandwidth	f _{3dB}	10458C	0.05	-	5	GHz
Impedance	Z	Resistively matched SMA connector	-	50	-	Ohm
S21 Flatness	-	50 MHz – 5 GHz	-	2	4	dB p-p

Specified characteristics apply for the recommended operating conditions at beginning of life, 25°C, unless noted otherwise.

10458C - 5 GHz





MICROWAVE

Ordering Information


Model Number	Description
10458C-SA	Receiver 5 GHz, SMA, AC Coupled, SC/APC
10458C-FA	Receiver 5 GHz, SMA, AC Coupled, FC/APC
10990A	System 10000 Equipment Chassis, 3 RU
10901G-NA	System 10000 Power Supply, US Power Cord
10901G-UK	System 10000 Power Supply, UK Power Cord
10901G-EU	System 10000 Power Supply, EU Power Cord

Pinout

Pin Number	Description
1	+15VDC
2	No Connection
3	No Connection
4	Ground
5 ¹	Ground
61	Photodiode Current Monitor 1v / 1 mA
71,2	Received Optical Power Alarm
81	No Connection
91	No Connection

^{1.} Pins 5 - 9 can be be monitored at the rear of the System 10000 chassis

Outline Drawing



Rev: December 10, 2010

^{2.} Open collector alarm, external 1K pull-up required. Capable of sinking 20 mA.