

BT-620

Bench-Top Particle Counter



The BT-620 is a compact battery operated particle counter with six selectable size channels, built-in printer, housed in a portable stainless steel case. Flow rate is 1.0 cfm (28.3 lpm) and is maintained with volumetric flow control for improved accuracy.

Simple Operation

The BT-620 has a large easy to read display, audio alarm, and internal printer that work together to verify particulate levels. If the particle count exceeds the users pre-set limit, the audible alarm will sound and the screen display, sample history and printout will indicate an alarm event. Two programmable count alarm limits may be set.

User Selectable Sizes

Each of the six channels may be individually set by the operator from 0.3 to 10 microns. Custom calibrations are not required.

Data Storage and Connectivity

The BT-620 stores over 8,000 sample events. Sample history events can be viewed or printed and downloaded to a computer using Particle View software or simple ASCII terminal commands. Connectivity is built-in for both digital (Ethernet, USB, RS-232, RS-485) and analog output (0-5 VDC). The BT-620 also includes a Memory Stick port.

Printer

The Printer has two modes of operation.

Print Sample: prints sample data at the end of each sample including alarm, date, time and location.

Recall Data: prints all sample data from first selected date and time to second selected date and time.

Portable Desk Top

The BT-620 provides 6 particle sizes, built-in printer and battery operation in a compact stainless steel case. The built-in battery provides over 8 hours of typical (intermittent) operation or 4 hours continuous operation. Connect the AC adapter/charger for longer operation and battery charging.

Temperature / Relative Humidity Option

A plug-and-play option can immediately add ambient temperature and relative humidity capabilities to displayed and logged data.



Applications:

- | | |
|------------------------------------|------------------------|
| Cleanroom Monitoring/Certification | Food / Beverage |
| Medical Device Mfg. | Aerospace Assembly |
| Filter Testing | Cosmetic Manufacturing |
| Hospitals | |

Whatever your particular needs,
The right choice is only natural.

PERFORMANCE

Particle Size Range	0.3µm - 10µm, 6 channels
Calibrated Sizes	0.3 µm, 0.5µm, 1.0µm, 2.0µm 5.0µm and 10µm
User Size Settings	0.1µm steps from 0.3µm - 2.0µm 0.5µm steps from 2.0µm - 10µm
Concentration Range	0 – 6,000,000 particles per cubic foot (over 20M particles/m3)
Accuracy	± 10% to calibration aerosol
Sensitivity	0.3 µm
Flow Rate	1.0 cfm (28.3 lpm)
Sample Time Adjustable:	1 to 999 seconds
Hold Time Adjustable:	0 to 999 seconds

ELECTRICAL

Light Source	Laser Diode, 90mW, 780 nm
Power	14.8V Li-Ion self-contained battery pack
Battery operation	Up to 8 hours typical or 4 hours continuous Full recharge approximately 3 hours
AC Adapter/Charger	Li-Ion Charger, 100 – 240 VAC @ 1.2A to 16.8 VDC @ 3.5A
Communications	USB, RS-232 or RS-485
Standards	Meets ISO 21501-4

INTERFACE

Display	20 character x 4 line LCD
Keyboard	8 key membrane type

PHYSICAL

Size	Height = 10.1" (25.7 cm) With Handle = 11.6" (29.5 cm) Width = 8" (20.3 cm) Depth = 9.5" (24.1 cm)
Weight	13.9 lbs (6.3 kg)

ENVIRONMENTAL


Operating Temperature	0° C to +40° C
Storage Temperature	-20° C to +60° C

ACCESSORIES

Supplied	Operation Manual (PN BT-620-9800) USB Cable (PN 500784) Comet Software (PN 80248) Particle View Software (PN PARTICLE VIEW) Battery Charger (PN 81751) Iso-kinetic Sample Probe (PN 81752) Zero Particulate Filter (PN 81754) Printer Paper - 2 Rolls (PN 750514)
----------	--

Optional

RH & Temperature Probe (PN G3120)
Flow Meter (PN 81755)
Serial Cable (PN 550065)
ISO 21501-4 Calibration (PN 80849)



1600 Washington Blvd., Grants Pass, OR 97526

Tel: 541.471.7111 | Fax: 541.471.7116

E-mail: handhelds@metone.com | www.metone.com