

Cree® 5-mm Oval LED Model # LO5SMTYL4-B0G-A Data Sheet

110-degree oval LED lamp in amber color with tinted, diffused lens and stopper

Applications

- Single-Color Display
- Indicators

Absolute Maximum Ratings $(T_A = 25^{\circ}C)$

Items	Symbol	Absolute Maximum Rating	Unit	
Forward Current	$I_{_{\rm F}}$	50	mA	
Peak Forward Current Note	$I_{\sf FP}$	200	mA	
Reverse Voltage	V_R	5	V	
Power Dissipation	P_{D}	130	mW	
Operation Temperature	T_{opr}	-40 ~ +95	°C	
Storage Temperature	T_{stg}	-40 ~ +100	°C	
Lead Soldering Temperature	T_{sol}	Max. 260° C for 3 sec. max. (3 mm from the base of the epoxy bulb)		

Note: Pulse width ≤ 0.1 msec, duty $\leq 1/10$.

Typical Electrical & Optical Characteristics $(T_A = 25^{\circ}C)$

Characteristics	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	$V_{\scriptscriptstyle F}$	$I_F = 20 \text{ mA}$	V		2.3	2.6
Reverse Current	I_R	$V_R = 5 V$	μΑ			100
Dominant Wavelength	$\lambda_{_{D}}$	$I_F = 20 \text{ mA}$	nm	584	591	596
Luminous Intensity	I_{v}	$I_F = 20 \text{ mA}$	mcd	390	600	
50% Power Angle	2θ1⁄2H-H	$I_F = 20 \text{ mA}$	deg		110	
	2θ1/2V-V	$I_F = 20 \text{ mA}$	deg		50	




Standard Bins for LO5SMTYL4-B0G-A ($I_F = 20 \text{ mA}$)

Lamps are sorted to luminous intensity (I_{v}) and dominant wavelength (λ_{n}) bins shown.

Orders for LO5SMTYL4-B0G-A may be filled with any or all bins contained as below.

All luminous intensity (I_v) and dominant wavelength (λ_D) values shown and specified are at I_F = 20 mA.





Important Notes:


- 1. All ranks will be included per delivery; rank ratio will be based on the dice distribution.
- 2. Pb content <1000 ppm.
- 3. Tolerance of measurement of luminous intensity is $\pm 15\%$.
- 4. Tolerance of measurement of dominant wavelength is ± 1 nm.
- 5. Tolerance of measurement of $V_{\rm F}$ is ± 0.05 V.
- 6. Packaging methods are available for selection; please refer to the "Cree LED Lamp Packaging Standard" document.
- 7. Please refer to the "Cree LED Lamp Reliability Test Standards" document for reliability test conditions.
- 8. Please refer to the "Cree LED Lamp Soldering & Handling" document for information about how to use this LED product safely.



Graphs












FIG.2 REVERSE CURRENT VS. REVERSE VOLTAGE.





50% Power Angle:

H-H: 110°

V-V : 50°

FIG.6 FAR FIELD PATTERN




Mechanical Dimensions

All dimensions are in mm. Tolerance is ± 0.25 mm unless otherwise noted.

An epoxy meniscus may extend about 1.5 mm down the leads.

Burr around bottom of epoxy may be 0.5 mm max.



Notes

RoHS Compliance

The levels of environmentally sensitive, persistent biologically toxic (PBT), persistent organic pollutants (POP), or otherwise restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2002/95/EC on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS), as amended through April 21, 2006.

Vision Advisory Claim


Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.



Kit Number System

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



^{*} Contact your Cree sales representative for ordering information.

Standard Available Kits*

Kit Number	Description			
LO5SMTYL4-B0G-A-00001	5mm Oval 110 Amber 591nm, FULL RANK, Bulk Pack			
LO5SMTYL4-B0G-A-00011	5mm Oval 110 Amber 591nm, R or above, Bulk Pack			

^{*} Please contact your Cree representative about the availability of non-standard kits.