



APD Hybrid Series Data Sheet Part Description AD500-9-8015-TO52 US Order # 05-100 International Order # 501403





### **FEATURES**

- $\varnothing$  0.500 mm active area
- · Low noise
- High gain
- · Long term stability

## **DESCRIPTION**

The AD500-9-8015-TO52 is an Avalanche Photodiode Amplifier Hybrid containing a 0.196 mm<sup>2</sup> active area APD chip integrated with an internal transimpedance amplifier. Hermetically packaged in a TO-52 with a flat borosilicate glass window cap.

## **APPLICATIONS**


- Precision photometry
- · Analytical instruments
- Medical equipment
- · Low light sensor




#### ABSOLUTE MAXIMUM RATING

7 125 0 20 1 2 107 0 101 10 1 1 1 1 1 1 1 1							
SYMBOL	PARAMETER	MIN	MAX	UNITS			
T <sub>STG</sub>	Storage Temp	-55	+125	°C			
Top	Operating Temp	0	+60	°C			
T <sub>SOLDERING</sub>	Soldering Temp	-	+240	°C			
Р	Power Dissipation	-	360	mW			
$V_{cc}$	Single Supply Voltage	+4.5	+11	٧			
lcc	Supply Current	_	26	mA			

## **SCHEMATIC**



## SPECTRAL RESPONSE at M = 100



## ELECTRO-OPTICAL CHARACTERISTICS @ 23° C (V<sub>CC</sub> = single supply +5V, R<sub>L</sub> = 50W unless otherwise specified)

SYMBOL	CHARACTERISTIC	TEST CONDITIONS	MIN	TYP	MAX	UNITS
f–3dB	Frequency Response	-3dB @ 905 nm		100		MHz
S	Sensitivity*	$\lambda = 905 \text{ nm}; M = 100$		1160		KV/W
I <sub>cc</sub>	Supply Current	Dark state		25	26	mA

 $<sup>^{\</sup>star}$  Sensitivity = APD responsivity (0.58 A/W X 100 gain) x TIA gain (20 K)

These devices are sensitive to electrostatic discharge. Please use ESD precautions when handling.

Disclaimer: Due to our policy of continued development, specifications are subject to change without notice.

#### AVALANCHE PHOTODIODE DATA @ 23 °C

SYMBOL	CHARACTERISTIC	TEST CONDITIONS	MIN	TYP	MAX	UNITS
I <sub>D</sub>	Dark Current	M = 100 (see note 2)		0.5	5.0	nA
С	Capacitance	M = 100 (see note 2)		1.2		pF
$V_{BR}$	Breakdown Voltage (see note 1)	$I_D = 2 \mu A$	160	240		V
	Temperature Coefficient of V <sub>BR</sub>			1.55		V/K
	Responsivity	$M = 100$ ; = 0 V; $\lambda = 905 \text{ nm}$	55	60		A/W
$\Delta f$ 3dB	Bandwidth	-3dB		0.5		GHz
t <sub>r</sub>	Rise Time	M = 100		550		ps
	Optimum Gain		50	60		
	"Excess Noise" factor	M = 100		2.5		
	"Excess Noise" index	M = 100		0.2		
	Noise Current	M = 100		1.0		pA/Hz1/2
	Max Gain		200			
NEP	Noise Equivalent Power	$M = 100; \lambda = 905 \text{ nm}$		2.0 X 10 <sup>-14</sup>		W/Hz1/2

- Note 1: The following different breakdown voltage ranges are available: (160 200 V), (200 240 V).
- Note 2: Measurement conditions: Setup of photo current 1 nA at M=1 and irradiated by a 880 nm, 80 nm bandwidth LED. Increase the photo current up to 100 nA, (M=100) by internal multiplication due to an increasing bias voltage.

#### TRANSIMPEDANCE AMPLIFIER DATA @ 25 °C

 $(Vcc = +4.5 \text{ V to } +11 \text{ V}, TA = 0^{\circ}\text{C to } 70^{\circ}\text{C}, 50\Omega \text{ load between OUT+ and OUT-. Typical values are at TA} = 25^{\circ}\text{C}, Vcc = +5 \text{ V})$ 

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage		+4.5	+5	+11	V
Supply Current			25	26	mA
Transimpedance	Differential, measured with 40 µA p-p signal	16	20	24	ΚΩ
Output impedance	Single ended per side	40	50	60	Ω
Maximum Differential Output Voltage	Input = 2 mA p-p with 50 $\Omega$ differential termination		600		mV p−p
Input Referred RMS Noise	TO-5 package, see note 4		26.5		nA
Input Referred Noise Density	See note 4		3.0		pA/Hz <sup>1/2</sup>
Small signal bandwidth	Source capacitance = 1.2 pF, see note 3	180	240		MHz
Low Frequency Cutoff	-3 dB, input < 20 μA DC		5		KHz
Transimpedance Linear Range	Peak to peak 0.95 < linearity < 1.05	±25	±30		µА р-р
Power Supply Rejection Ratio (PSRR)			40		dB

- Note 3: Source capacitance for AD500-9-8015-TO52 is the capacitance of APD.
- Note 4: Input referred noise is calculated as RMS output noise/ (gain at f = 100 Mhz). Noise density is (input referred noise)/ $\sqrt{bandwidth}$ .

#### TRANSFER CHARACTERISTICS

The circuit used is an avalanche photodiode directly coupled to a high speed data handling transimpedance amplifier. The output of the APD (light generated current) is applied to the input of the amplifier. The amplifier output is in the form of a differential voltage pulsed signal.

The APD responsivity curve is provided in Fig. 2. The term Amps/Watt involves the area of the APD and can be expressed as Amps/mm²/Watts/mm², where the numerator applies to the current generated divided by the area of the detector, the denominator refers to the power of the radiant energy present per unit area. As an example assume a radiant input of 1 microwatt at 850 nm. The APD's corresponding responsivity is 0.4 A/W.

If energy in = 1  $\mu$ W, then the current from the APD =  $(0.4 \text{ A/W}) \times (1 \times 10^{-6}\text{W}) = 0.4 \mu$ A. We can then factor in the typical gain of the APD of 100, making the input current to the amplifier 40  $\mu$ A.

#### **APPLICATION NOTES**


The AD500-9-8015-TO52 is a high speed optical data receiver. It incorporates an internal transimpedance amplifier with an avalanche photodiode.

This detector requires +4.5 V to +11 V voltage supply for the amplifier and a high voltage supply (100-240 V) for the APD. The internal APD follows the gain curve published for the AD500-9-TO52-S1 avalanche photodiode. The transimpedance amplifier provides differential output signals in the range of 200 millivolts differential.

In order to achieve highest gain, the avalanche photodiode needs a positive bias voltage (Fig. 1). However, a current limiting resistor must be placed in series with the photodiode bias voltage to limit the current into the transimpedance amplifier. **Failure to limit this current may result in permanent failure of the device.** The suggested initial value for this limiting resistor is 390 KOhm.

When using this receiver, good high frequency placement and routing techniques should be followed in order to achieve maximum frequency response. This includes the use of bypass capacitors, short leads and careful attention to impedance matching. The large gain bandwidth values of this device also demand that good shielding practices be used to avoid parasitic oscillations and reduce output noise.

# Fig. 1: APD GAIN vs BIAS VOLTAGE



# Fig. 2: APD SPECTRAL RESPONSE (M = 1)




Fig. 3: AMPLIFIER BANDWIDTH vs TEMPERATURE




Fig.4: APD CAPACITANCE vs VOLTAGE




Fig. 5: DIFFERENTIAL GAIN vs. SUPPLY





Fig. 6: AMPLIFIER GAIN vs. FREQUENCY





# USA

First Sensor Inc. 5700 Corsa Avenue, #105 Westlake Village, CA 91362 USA T + 818 706-3400 F + 818 889-7053 contact.us@first-sensor.com www.first-sensor.com

### International sales

First Sensor AG
Peter-Behrens-Str. 15
12459 Berlin, Germany
T + 49 30 6399 2399
F + 49 30 639923-752
sales.opto@first-sensor.com
www.first-sensor.com